





Transformer, dry type, encapsulated, 10kVA, 1 phase, multiple voltages, 13B, 115C rise

10S67F

Product availability: Stock - Normally stocked in distribution facility

Price*: 5,406.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	190/200/208/220 x 380/400/416/440 V 110/220 V
Full Capacity Taps	0

Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	10 kVA
Temperature Rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Insulation Temperature	356 °F (180 °C)
Product Certifications	CSA UL Listed cULus TÜV

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901069508
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	15.00 in (38.1 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	10.00 in (25.4 cm)
Package 1 Weight	165.00 lb(US) (74.843 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov