





Transformer, dry type, encapsulated, 1kVA, 1 phase, 240x480V primary, 120/240V secondary, 7A, 115C rise

1S1F

Product availability: Stock - Normally stocked in distribution facility

Price*: 813.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	240 x 480 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	7A
Phase	1 phase
Power Rating	1 kVA
Temperature Rise	115 °C
Height	8.13 in (206.50 mm)
Width	6.94 in (176.28 mm)
Depth	5.31 in (134.87 mm)
Enclosure Mounting	Wall mounted
Net Weight	21.2 lb(US) (9.62 kg) 21.21 lb(US) (9.62 kg)
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed cULus CSA

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901019862
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.80 in (22.352 cm)
Package 1 Width	10.50 in (26.67 cm)
Package 1 Length	11.20 in (28.448 cm)
Package 1 Weight	0.38 oz (10.705 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	44
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1090.00 lb(US) (494.415 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov