





Transformer, buck boost, encapsulated, 1kVA, 1 phase, 120x240V primary, 16/32V secondary, NEMA 3R, 115C rise

1S46F

Product availability: Stock - Normally stocked in distribution facility

Price*: 913.00 USD

Main

| Product | Buck and Boost Transformer |
|------------------------|----------------------------|
| Enclosure Code | 7A |
| Enclosure Type | NEMA 3R |
| Insulation Temperature | 356 °F (180 °C) |
| Primary Voltage | 120 x 240 V |
| Power Rating | 1 kVA |
| Secondary Voltage | 16/32 V |
| Temperature Rise | 115 °C |

Ordering and shipping details

| Category | US10PE216265 0PE2 | |
|-------------------|----------------------|--|
| Discount Schedule | | |
| Gtin | 785901876328 | |
| Returnability | Yes | |
| Country Of Origin | MX | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 9.10 in (23.114 cm) |
| Package 1 Width | 10.50 in (26.67 cm) |
| Package 1 Length | 11.60 in (29.464 cm) |
| Package 1 Weight | 24.95 lb(US) (11.317 kg) |

Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|--------------------------------|
| ⊘ | Toxic Heavy Metal Free |
| ⊘ | Mercury Free |
| ② | Rohs Exemption Information Yes |
| ⊘ | Pvc Free |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant |
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |