

Product data sheet

Specifications

SQUARE D



FHP Manual Starter - NEMA 1 Oversized - 1P-Toggle Operated-Red Indicator-277VAC

2510FGJ1P

Discontinued on: Jun 30, 2020

Discontinued

Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Current Rating	16 A
Cable Entry	0.5" or 0.75" knock-outs (2 side)
Horsepower Rating	1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC
Voltage Rating	277 V AC
Number Of Poles	1P
Control Unit	Toggle switch
Number Of Phases	1 phase
Pilot Light	Red indicator
Reset	Manual
Motor Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.25 in (107.95 mm)
Width	2.88 in (73.15 mm)
Depth	2.75 in (69.85 mm)

Environment

Product Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	NEMA 1 Plastic oversized

Ordering and shipping details

Category	21101-2510,2511,2512 F
Discount Schedule	CP1
Gtin	00785901856832

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc

 Pvc Free

Eu Rohs Directive

Not compliant

China Rohs Regulation

[China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov