

# Product data sheet

Specifications

SQUARE D



## Manual Switch - NEMA 4 - 2P - Toggle Operated - Red Indicator - 600VAC

2510KW5BH

⚠ Discontinued on: Nov 11, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Current Rating	30 A
Cable Entry	0.75 NPT (top and bottom)
Horsepower Rating	2 hp 115 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC 10 hp 575 V AC 3 hp 230 V AC 7.5 hp 460 V AC
Maximum Voltage Rating	600 V AC 230 V DC
Number Of Poles	2P
Control Unit Type	Toggle
Number Of Phases	1 phase
Pilot Light	Red indicator, 230 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.38 in (111.25 mm)
Width	3 in (76.20 mm)
Depth	4.56 in (115.82 mm)

### Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	NEMA 4 die cast zinc alloy standard size

### Ordering and shipping details

Category	US10CP121102
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0CP1
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc

 Pvc Free

## Eu Rohs Directive

Not compliant

## China Rohs Regulation

### China RoHS declaration

Product out of China RoHS scope. Substance declaration for your information.

## California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)