

Product data sheet

Specifications



Manual starter, integral horsepower, NEMA M0, 600VAC, 2 pole, 2HP at 230VAC, 1 phase, no indicator, NEMA 4/4X

2510MBW11

Product availability: Stock - Normally stocked in distribution facility

Price*: 756.53 USD

Main

Product	Manual Starter
Type	M
Nema Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	1 hp 115 V AC, 1 phase 2 hp 230 V AC, 1 phase
Voltage Rating	600 V AC
Number Of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	10.92 in (277.37 mm)
Width	5.78 in (146.81 mm)
Depth	5.76 in (146.30 mm)

Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
Nema Enclosure Rating	NEMA 4/4X brushed stainless steel

Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1
Gtin	785901057642

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.10 in (15.5 cm)
Package 1 Width	6.69 in (17.0 cm)
Package 1 Length	11.42 in (29.0 cm)
Package 1 Weight	7.50 lb(US) (3.4 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov