

Product data sheet

Specifications



Manual Starter - Open Device - Buttons - 2P - Size M1 - 600VAC

2510MCO1

Discontinued on: Jun 30, 2020

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Manual Starter
Type	M
Nema Size	M-1

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	2 hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase
Voltage Rating	600 V AC
Number Of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	5.72 in (145.29 mm)
Width	3.5 in (88.90 mm)
Depth	4.03 in (102.36 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
Nema Enclosure Rating	Not rated (open device)

Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1
Gtin	00785901792123
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	