Product data sheet

Specifications





voltage release - MN - 48 V AC / 48 Vdc - UL

27106

Discontinued on: Jan 23, 2021

! Discontinued

Main

Range Of Product	Multi9
Product Or Component Type	Undervoltage release
Device Short Name	MN
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC
Control Type	Standard
9 Mm Pitches	2

Complementary

Range Compatibility	Multi9 Multi9 C60 Multi9 Multi9 C60H-DC
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Connections - Terminals	Clamp terminal - 1 0.00 in² (2.5 mm²) - flexible Clamp terminal - 1 0.00 in² (2.5 mm²) - rigid Clamp terminal - 2 0.00 in² (1.5 mm²) - flexible Clamp terminal - 2 0.00 in² (1.5 mm²) - rigid
Wire Stripping Length	0.35 in (9 mm)
Tightening Torque	8.85 lbf.in (1 N.m)

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	ASEFA ASTA LCIE KEMA
Tropicalisation	2 EN/IEC 60947-5-1
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00908-C60N SUPPLEMENTARY PROTECTORS
Discount Schedule	DE2
Gtin	00785901409632
Returnability	No
Country Of Origin	BE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9 cm)
Package 1 Width	0.94 in (2.4 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	2.54 oz (72 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
	Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	