## **Product data sheet**

Specification





# voltage release - MNx - 380..415 V AC

26971

! Discontinued on: Feb 17, 2021

! Discontinued

### Main

Range Of Product	Multi9
Product Or Component Type	Undervoltage release
Device Short Name	MNx
[Uc] Control Circuit Voltage	400 V AC 50/60 Hz
Control Type	With external feeding
9 Mm Pitches	2

## Complementary

Range Compatibility	Multi9 Multi9 C60 Multi9 Multi9 ID Multi9 Multi9 N40 Acti 9 Acti9 iDPN
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Connections - Terminals	Clamp terminal - 1 0.00 in² (2.5 mm²) - flexible
Wire Stripping Length	0.35 in (9 mm)
Tightening Torque	8.85 lbf.in (1 N.m)

## **Environment**

Standards	EN/IEC 60947-5-1
Product Certifications	ASEFA KEMA LCIE
	ASTA
Tropicalisation	2 EN/IEC 60947-5-1
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Gtin 3303430269717

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	2.96 oz (84 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
	Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	