

Product data sheet

Specifications



Removable toggle padlocking device, ComPacT NSX, PowerPacT B, EasyPacT CVS, OFF position only

29370

Product availability: Stock - Normally stocked in distribution facility

Price*: 116.00 USD

Main

Range Compatibility	ComPact ComPact NSXm ComPact ComPact NSX100 ComPact ComPact NSX160 ComPact ComPact NSX250 ComPact ComPact NSX400 ComPact ComPact NSX630 EasyPact EasyPact CVS100 EasyPact EasyPact CVS160 EasyPact EasyPact CVS250 PowerPact PowerPact B TeSys TeSys GV4 TeSys TeSys BV4 ComPact Compact NSX100 DC ComPact Compact NSX160 DC ComPact Compact NSX250 DC ComPact Compact NSF250 ComPact Compact NSJ400 ComPact Compact NSJ600 ComPact Compact NSX500 ComPact Compact NB400 ComPact Compact NB600
Product Or Component Type	Padlocking device
Device Short Name	locking for 1 to 3 padlocks

Complementary

Accessory / Separate Part Type	Keylock accessories
Mounting Mode	Removable
Keylock Destination	Toggle
Number Of Locks	3
Key Locking Position	In front
Locking Options Description	Lock OFF only 1 to 3 padlocks Removable

Ordering and shipping details

Category	US10DE200924
Discount Schedule	0DE2
Gtin	3303430293705
Returnability	Yes
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.000 cm)
Package 1 Width	3.07 in (7.800 cm)
Package 1 Length	3.58 in (9.100 cm)
Package 1 Weight	1.48 oz (42.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	40
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	4.60 lb(US) (2.087 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	320
Package 3 Height	19.69 in (50.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	63.26 lb(US) (28.696 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65		WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov