





Transformer, dry type, encapsulated, 30kVA, 3 phase, 480V delta primary, 208Y/120V secondary, 16C, 115C rise

30T2FSS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 15,627.00 USD

#### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	480 V delta 208Y/120 V
Full Capacity Taps	2 5 % FCBN

# Complementary

Enclosure Code	16C
Phase	3 phase
Power Rating	30 kVA
Temperature Rise	115 °C
Height	22 in (558.80 mm)
Width	25 in (635.00 mm)
Depth	13.5 in (342.90 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Stainless Steel

#### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	cULus CSA UL Listed

### Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901015376
Returnability	No
Country Of Origin	US

### **Packing Units**

Unit <sup>-</sup>	Type Of	Package 1	PCI
Unit <sup>-</sup>	Type Of	Package 1	PC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	16.40 in (41.656 cm)
Package 1 Width	25.50 in (64.77 cm)
Package 1 Length	21.30 in (54.102 cm)
Package 1 Weight	775.00 lb(US) (351.534 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov