Product data sheet

Specification





MN delay unit, MasterPact NT/ NW, ComPacT NS, adjustable time delay 0.5s/3s, 100/130VDC, 100/130VAC 50/60Hz, spare part

33681

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,140.00 USD

Main

MN delay unit
Time delay relay
Control
Masterpact MasterPact NT
Masterpact MasterPact NW
ComPact ComPact NSX
ComPact ComPact NS630b1600
ComPact ComPact NS1600b3200
PowerPact PowerPact Multistandard
ComPact ComPact NSXm
ComPact ComPact NSX DC
Masterpact MasterPact NW UL 489
Masterpact MasterPact NT UL 489
Masterpact MasterPact NW DC
Undervoltage release
100130 V AC 50/60 Hz 100130 V DC

Complementary

J		
Impulse Duration	200 ms	
Time Delay Range	0.53 s	
Threshold Tripping Voltage	0.350.7 Un open 0.85 Un close	
Supply Holding Power	4.5 VA	
Supply Inrush Power	200 VA	
Mounting Mode	External mounting	
Response Time	0.5 s 1 s 1.5 s 3 s	
Accessory / Separate Part Category		

Ordering and shipping details

Category	US1DE2F01291
Discount Schedule	DE2F
Gtin	3303430336815

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	6.77 oz (192.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	16.12 lb(US) (7.31 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov