Product data sheet

Specifications

SQUARE D





Transformer, dry type, encapsulated, 3kVA, 1 phase, 600V primary, 120/240V secondary, 10A, 115C rise

3S4F

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,674.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	600 V 120/240 V
Full Capacity Taps	2 5 % FCBN

Complementary

eempromonical	J
Enclosure Code	10A
Phase	1 phase
Power Rating	3 kVA
Temperature Rise	115 °C
Height	10.5 in (266.70 mm)
Width	8.62 in (218.95 mm)
Depth	6.5 in (165.10 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed cULus CSA

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901359548
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	12.20 in (30.988 cm)
Package 1 Width	11.40 in (28.956 cm)
Package 1 Length	17.30 in (43.942 cm)
Package 1 Weight	59.35 lb(US) (26.921 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov