





Transformer, dry type, encapsulated, 3kVA, 3 phase, 480V primary, 208Y/120V secondary, 12C, 115C rise

3T2F

Product availability: Stock - Normally stocked in distribution facility

Price\*: 2,924.00 USD

#### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	480 V delta 208Y/120 V
Full Capacity Taps	2 5 % FCBN

## Complementary

Enclosure Code	12C
Phase	3 phase
Power Rating	3 kVA
Temperature Rise	115 °C
Height	13.5 in (342.90 mm)
Width	14.75 in (374.65 mm)
Depth	9 in (228.60 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

#### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	CSA cULus III Listed

## Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901359463
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	11.70 in (29.72 cm)
Package 1 Width	14.00 in (35.56 cm)
Package 1 Length	15.00 in (38.1 cm)
Package 1 Weight	118.17 lb(US) (53.6 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Reach Free Of Svhc
<b>Ø</b>	Toxic Heavy Metal Free
<b>Ø</b>	Mercury Free
<b>Ø</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov