

499NSS25102

Ethernet TCP/IP switch - ConneXium - 3 ports for copper + 2 for fiber optic

Price* : 3,410.00 USD



⚠ Discontinued

499NSS25102 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	100BASE-FX - 2 port(s) fiber optic 10BASE-T/100BASE-TX - 3 port(s) copper cable
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	SC fiber optic Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E copper cable Single mode optical fiber fiber optic
Attenuation	16 dB 9/125 μm
Redundancy	P1 and P2 redundant power supplies
[Us] rated supply voltage	24 V
Supply voltage limits	18...32 V DC SELV
Power consumption in W	5.9 W
Electrical connection	Removable connector 5 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE
Local signalling	1 LED fault 1 LED per channel Ethernet link active 2 LEDs P1 P2 power supplies
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Data link status Switch fault
Ethernet cabling system	TF switches
Current consumption	<= 240 mA 24 V DC
Width	1.85 in (47 mm)
Height	5.31 in (135 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	4.37 in (111 mm)
Product weight	0.74 lb(US) (0.335 kg)

Environment

Ambient air temperature for operation	32...140 °F (0...60 °C)
Relative humidity	0...95 % without condensation
IP degree of protection	IP20
Standards	UL 508 CUL 60950 UL 1604 CSA C22.2 No 142 CSA C22.2 No 213 Class I Division 2

Ordering and shipping details

Category	18225 - PLC NTRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	00785901426219
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0626 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------