





Transformer, dry type, encapsulated, 5kVA, 1 phase, 480V primary, 120/240V secondary, 13B, 115C rise

5S40FSS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 5,238.00 USD

### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	480 V 120/240 V
Full Capacity Taps	2 5 % FCBN

# Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	5 kVA
Temperature Rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Stainless Steel

### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed cULus CSA

## Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901765950
Returnability	No
Country Of Origin	US

## **Packing Units**

Unit <sup>-</sup>	Type Of	Package 1	PCI
Unit <sup>-</sup>	Type Of	Package 1	PC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	11.22 in (28.499 cm)
Package 1 Width	10.24 in (26.01 cm)
Package 1 Length	13.23 in (33.604 cm)
Package 1 Weight	115.00 lb(US) (52.163 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov