Product data sheet

Specifications



Power Relay, SPST, 1NO and 0NC, 20 A resistive at 110 VDC, 6 VAC coil

8501CO21V35

() Discontinued on: Dec 2, 2020

() Discontinued

(!) End-of-service on: Dec 31, 2020

Main

Product Range	Power Relay 8501C
Product Type	Power relay
Short Name	type C
[In] Rated Line Current	20 A
Device Application	Suited for controlling small single phase motors and other light loads
Switch Function	SPST
Contact Composition	1 NO
[Uc] Control Circuit Voltage	6 V AC 50/60 Hz
Maximum Switching Voltage	500 V DC

Complementary

Class Number	8501	
Phase	1 phase	
Terminal Connects	Screw clamp terminal	
Wire Range	AWG 10 copper	
Terminal Tightening Torque	1115 lbf.in (1.241.69 N.m)	
Coil Burden	10 VA	
Mounting	Panel mounting	

Environment

Ambient Temperature Range - Operational	-22122 °F (-3050 °C)
Product Certifications	UL listed file E78351 CCN NLDX CSA CE
Height	2.43 in (61.72 mm)
Width	2.5 in (63.50 mm)
Depth	2.18 in (55.37 mm)

Ordering and shipping details

Category	21131-8501 C
Discount Schedule	CP2

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov