

Product data sheet

Specifications

SQUARE D

Green Premium™



Safety switch, double throw, non fusible, 200A, 600V, 3 pole, 15hp, NEMA 1

82344

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,783.00 USD

Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number Of Poles	3
Current Rating	200 A
Voltage Rating	480 V AC 250 V DC
Enclosure Rating	NEMA 1
Motor Power Hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors

Complementary

Short-Circuit Current	10 kA H or J
Fuse Type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening Torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	11.75 in (298.45 mm)
Width	23.88 in (606.55 mm)
Height	30.88 in (784.35 mm)
Net Weight	64.07 lb(US) (29.06 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	US10DE100033
Discount Schedule	0DE1
Gtin	785901453772
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.00 in (30.48 cm)
Package 1 Width	24.50 in (62.23 cm)
Package 1 Length	32.00 in (81.28 cm)
Package 1 Weight	62.74 lb(US) (28.458 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	6
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	376.77 lb(US) (170.901 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov