





# NEMA Control Relay, Type X, mechanical latch attachment, 110/120VAC 50/60Hz coil

8501XLV02

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 169.00 USD

#### Main

Range Of Product	8501X
Relay Type	Control relay
Product Or Component Type	Latching device

#### Complementary

Complementary	
[Uc] Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Coil Voltage Limits	Operational 0.851.1 Uc AC 50/60 Hz
Coil Inrush Power	148 VA 60 Hz 143 VA 50 Hz
Coil Sealed Power	23 VA 60 Hz 25 VA 50 Hz
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18AWG 12 copper
Terminal Tightening Torque	Control circuit 9.0312.04 lbf.in (1.021.36 N.m) screw terminals
Height	2.87 in (73 mm)
Width	2.24 in (57 mm)
Depth	2.95 in (75 mm)
Net Weight	0.76 lb(US) (0.3425 kg)

## **Environment**

<b>Product Certifications</b>	UL recognized E78403 CCN NKCR2
	CE
	CSA LR60905 class 3211 02

## Ordering and shipping details

Category	US10CP221159
Discount Schedule	0CP2
Gtin	785901028475
Returnability	No
Country Of Origin	MX

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	14.24 oz (403.697 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov