

# Product data sheet

Specifications

SQUARE D



## RELAY 600VAC 10AMP NEMA +OPTIONS

8501XO40XLV01

Discontinued on: Oct 11, 2019

Discontinued

### Main

|                       |                                     |
|-----------------------|-------------------------------------|
| Range                 | 8501X                               |
| Relay Type            | Latching                            |
| Product               | Relay                               |
| Current Rating        | 10 A AC<br>5 A DC                   |
| Contact Configuration | 4 NO 4 standard contact cartridges  |
| Number Of Poles       | 4P                                  |
| Coil Voltage          | 24 V AC 60 Hz                       |
| Voltage Rating        | 600 V AC                            |
| Mounting Type         | Panel                               |
| Operating Temperature | -40...160 °F (-40...71 °C)          |
| Electrical Connection | Screw clamp terminals               |
| Certifications        | CSA<br>UL Listed<br>CE              |
| Operating Time        | 15 ms - pick-up<br>13 ms - drop-out |
| Height                | 3.50 in (88.90 mm)                  |
| Width                 | 2.23 in (56.64 mm)                  |
| Depth                 | 6.54 in (166.12 mm)                 |

### Ordering and shipping details

|                   |                    |
|-------------------|--------------------|
| Category          | 21158-8501 XO (AC) |
| Discount Schedule | CP2                |
| Gtin              | 00785901836094     |
| Returnability     | No                 |
| Country Of Origin | MX                 |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |