

# Product data sheet

Specifications

SQUARE D



NEMA Contactor, Type S, nonreversing, Size 1, 27A, 3 HP at 230 VAC, 1 phase, up to 100 kA, 1 pole, 240 VAC coil, NEMA 1

8502SCG5V03

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|                |               |
|----------------|---------------|
| Product Type   | Contactor     |
| Product Range  | 8502S         |
| Contactor Type | Non-reversing |

## Complementary

|                        |  |
|------------------------|--|
| Nema Size              | 1  |
| Rated Current          | 27 A   |
| Number Of Poles        | 1P   |
| Maximum Voltage Rating | 600 V AC   |
| Phase                  | 1 phase  |
| Horsepower Rating      | 3 HP 230 V AC<br>2 HP 115 V AC   |
| Sccr                   | Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC<br>Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC<br>Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC<br>Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC<br>Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC |
| Coil Voltage           | 240 V AC 60 Hz<br>220 V AC 50 Hz   |
| Control Circuit Type   | Common control circuit   |
| Control Units          | No control units   |
| Pilot Light            | No indicator   |
| Auxiliary Contacts     | Without  |
| Other Equipment        | Fuse not supplied  |
| Terminal Type          | Screw clamp terminals  |
| Height                 | 10.00 in (254 mm)  |
| Width                  | 5.98 in (152 mm)   |
| Depth                  | 5.28 in (134 mm)   |

## Environmental

|                |                                       |
|----------------|---------------------------------------|
| Enclosure Type | NEMA 1 painted sheet steel            |
| Certifications | UL listed file E78351 CCN NLDX<br>CSA |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 21192 - 8502,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1                                |
| Gtin              | 785901312611                       |
| Returnability     | No                                 |
| Country Of Origin | MX                                 |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 10.00 in (25.4 cm)     |
| Package 1 Width              | 5.98 in (15.2 cm)      |
| Package 1 Length             | 5.28 in (13.4 cm)      |
| Package 1 Weight             | 5.00 lb(US) (2.268 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

|                           |   |
|---------------------------|---|
| Eu Rohs Directive         | Not compliant   |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |