

# Product data sheet

Specifications



NEMA Motor Starter, Type S, nonreversing, Size 0, 18A, 5 HP at 460 VAC, 5 kA SCCR, 3 phase, 3 pole, melting alloy, 480 VAC coil, NEMA 12

8536SBA2V06

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 689.00 USD

## Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

## Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	12.75 in (323.85 mm)
Width	6.38 in (162.05 mm)
Depth	8.53 in (216.66 mm)

## Environment

Enclosure Type	NEMA 12 painted sheet steel
----------------	-----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

## Ordering and shipping details

Category	US10CP121191
Discount Schedule	0CP1
Gtin	785901877134
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.10 in (18.034 cm)
Package 1 Width	8.30 in (21.082 cm)
Package 1 Length	13.10 in (33.274 cm)
Package 1 Weight	12.50 lb(US) (5.67 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Pvc Free

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>