

# Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S, nonreversing, Size 1, 27A, 3 HP at 230 VAC, 5 kA SCCR, 1 phase, 2 pole, melting alloy, 240 VAC coil, NEMA 4X

8536SCW21V03

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

## Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	12.13 in (308.10 mm)
Width	6.50 in (165.10 mm)
Depth	6.44 in (163.58 mm)

## Environment

Enclosure Type	NEMA 4X glass polyester
----------------	-------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

## Ordering and shipping details

Category	21202 - 8502,36 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.13 in (30.8 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	6.46 in (16.4 cm)
Package 1 Weight	33.25 lb(US) (15.082 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Pvc Free

Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>