

# Product data sheet

Specifications

SQUARE D



NEMA Contactor, Type S, reversing, vertical, Size 0, 18A, 5 HP at 575 VAC, 3 phase, up to 100 kA, 3 pole, 480 VAC coil, open style

8702SBO12V06

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

## Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Sccr	Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	No indicator
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	9.22 in (234.19 mm)
Width	5.47 in (138.94 mm)
Depth	5.31 in (134.87 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

## Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.21 in (23.4 cm)
Package 1 Width	5.47 in (13.9 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	11.00 lb(US) (4.99 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>