

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, vertical, Size 0, 18A, 2 HP at 230 VAC, 5 kA SSCR, 1 phase, 3 pole, melting alloy overload, 24 VAC coil, open

8736SBO9V01

To be discontinued

To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------|-----------|
| Product Type | Starter |
| Product Range | S |
| Starter Type | Reversing |

Complementary

| | |
|------------------------|-------------------------------------------------------------|
| Nema Size | 0 |
| Rated Current | 18 A |
| Number Of Poles | 3P |
| Mounting Orientation | Vertical |
| Wiring Mode | 4 wires |
| Maximum Voltage Rating | 600 V AC |
| Phase | 1 phase |
| Motor Type | Split phase |
| Type Of Overload | Melting alloy 1 |
| Horsepower Rating | 1 HP 115 V AC 2 HP 230 V AC |
| Sscr | Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC |
| Coil Voltage | 24 V AC 60 Hz |
| Control Circuit Type | Common control circuit |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Terminal Type | Screw clamp terminals |
| Height | 11.52 in (292.61 mm) |
| Width | 5.47 in (138.94 mm) |
| Depth | 5.31 in (134.87 mm) |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|-------------------------|
| Enclosure Type | Not rated (open device) |
| Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21271 - 8702,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 11.54 in (29.3 cm) |
| Package 1 Width | 5.47 in (13.9 cm) |
| Package 1 Length | 5.31 in (13.5 cm) |
| Package 1 Weight | 7.95 lb(US) (3.606 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

| | |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Under investigation |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |