





Contactor, Type L, multipole lighting, electrically held, 30A, 6 pole, 600 V, 440/480 VAC 50/60 Hz coil, NEMA 3R/12

8903LA60V06

! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz
Hold-In Power Consumption In Va	30 VA 60 Hz 30 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	6P 6 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	15.75 in (400 mm)
Depth	8.50 in (216 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.75 in (40.0 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	8.50 in (21.6 cm)
Package 1 Weight	21.78 lb(US) (9.879 kg)

Contractual warranty

Warranty 18 months

Apr 25, 2024



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations