## Product data sheet

Specifications



# 8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 1

8903LXG60V04A3

Discontinued on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Mechanically Held Lighting Contactor	
Range Of Product	8903LX	
Control Circuit	Separate control circuit	

#### Complementary

oompiementary	y .	
Control Voltage	277 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	6P 6 NO	
Control Unit	Push-button ON) Push-button OFF)	
Pilot Light	No indicator	
Other Options	None	
Electrical Connection	Screw-clamp terminals	
Height	12.68 in (322 mm)	
Depth	6.02 in (153 mm)	
Width	7.80 in (198 mm)	

#### Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

## Ordering and shipping details

Category	21322 - 8903 LX (NOT L)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

## **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.50 in (19.05 cm)
Package 1 Width	8.00 in (20.32 cm)
Package 1 Length	13.50 in (34.29 cm)
Package 1 Weight	13.89 lb(US) (6.302 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov