Product data sheet

Specifications



Contactor, Type L, multipole lighting, mechanically held, 30A, 8 pole, 600V, 110/120VAC 50/60Hz coil, open style

() Discontinued on: Sep 15, 2023

() To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Other Options	2P relay (1 NO + 1 NC)	
Electrical Connection	Screw-clamp terminals	
Height	8.82 in (224 mm)	
Depth	3.27 in (83 mm)	
Width	5.63 in (143 mm)	

Environment

Enclosure Type	Not rated (open device)	
Product Certifications	UL Listed CSA	

Ordering and shipping details

Category	US10CP121322	
Discount Schedule	0CP1	
Gtin	785901023494	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	10.50 in (26.67 cm)
Package 1 Weight	9.75 lb(US) (4.421 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov