





(!) Discontinued

8903L electrically held lighting contactor, 2 P, 2 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 1, selector switch

8903LG20V04C

(

(!) Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 782.00 USD

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	277 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz	
Hold-In Power Consumption In Va	30 VA 60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	2P 2 NO	
Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	12.68 in (322 mm)	
Depth	6.02 in (153 mm)	
Width	7.80 in (198 mm)	

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Gtin	785901022619	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.50 in (19.05 cm)	
Package 1 Width	8.00 in (20.32 cm)	
Package 1 Length	13.50 in (34.29 cm)	
Package 1 Weight	12.58 lb(US) (5.706 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov