





Contactor, Type L, multipole lighting, electrically held, 30A, 10 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 1

8903LG307V02

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

Complementary	Complementary		
Control Circuit Voltage	110 V AC 50 Hz		
	120 V AC 60 Hz		
Inrush Power In Va	180 VA 60 Hz		
	170 VA 50 Hz		
Hold-In Power Consumption In Va	35 VA 60 Hz		
	35 VA 50 Hz		
Current Rating	20 A tungsten		
	30 A fluorescent		
Number Of Poles	3P 3 NO		
Control Unit	No control units		
Pilot Light	No indicator		
Electrical Connection	Screw-clamp terminals		
Height	12.68 in (322 mm)		
Depth	6.02 in (153 mm)		
Width	7.80 in (198 mm)		

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	7.50 in (19.05 cm)
Package 1 Width	13.50 in (34.29 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	6.00 lb(US) (2.722 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations