

# Product data sheet

Specifications



Contactor, Definite Purpose, 30A, 2 pole, 5HP at 230VAC, 1 phase, 208/240VAC 60Hz 220VAC 50Hz coil, open

8910DPA32V09

Product availability: Stock - Normally stocked in distribution facility

Price\*: 91.38 USD

## Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number Of Poles	2P
Pole Contact Composition	2 NO
Range Of Product	DPA

## Complementary

Maximum Horse Power Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked Rotor Rated Current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Binder head

## Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

## Ordering and shipping details

Category	US1CP1B21343
Discount Schedule	CP1B
Gtin	785901749813
Returnability	Yes
Country Of Origin	CN

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	15.68 oz (444.521 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.