

Product data sheet

Specifications



Contactor, Definite Purpose, 40A, 2 pole, 7.5HP at 230VAC, 1 phase, 110/120VAC 50/60Hz coil, open

8910DPA42V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 101.75 USD

Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number Of Poles	2P
Pole Contact Composition	2 NO
Range Of Product	DPA

Complementary

Maximum Horse Power Rating	3 hp 115 V AC, 1 phase 7.5 hp 230 V AC, 1 phase
Locked Rotor Rated Current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical Connection	Box lugs Quick connect terminals

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	US1CP1B21344
Discount Schedule	CP1B
Gtin	785901073475
Returnability	Yes
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.52 in (6.4 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	4.02 in (10.2 cm)
Package 1 Weight	16.19 oz (459 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	6.81 in (17.3 cm)
Package 2 Width	5.31 in (13.5 cm)
Package 2 Length	8.11 in (20.6 cm)
Package 2 Weight	8.37 lb(US) (3.797 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.