

# Product data sheet

Specifications



Contactor, Definite Purpose, 75A, 2 pole, 15HP at 230VAC, 1 phase, 24/24VAC 50/60Hz coil, open

8910DPA72V14

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 284.50 USD

## Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	75 A
Number Of Poles	2P
Pole Contact Composition	2 NO
Range Of Product	DPA

## Complementary

Maximum Horse Power Rating	5 hp 115 V AC, 1 phase 15 hp 230 V AC, 1 phase
Locked Rotor Rated Current	450 A 277 V AC 375 A 460 V AC 300 A 575 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical Connection	Box lugs Quick connect terminals

## Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

## Ordering and shipping details

Category	US1CP1B21347
Discount Schedule	CP1B
Gtin	785901024538
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.40 in (16.256 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	6.00 in (15.24 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	3.31 lb(US) (1.501 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.