

# Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 3 pole, NEMA 1, 277V 60Hz

8903SMG11V04

Discontinued

Discontinued on: Dec 12, 2019

End-of-service on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|         |                                      |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type    | S                                    |

## Complementary

|                         |                     |
|-------------------------|---------------------|
| Control Circuit Voltage | 277 V AC 60 Hz      |
| Current Rating          | 30 A                |
| Number Of Poles         | 3P                  |
| Control Units           | No control units    |
| Pilot Light             | Without pilot light |
| Auxiliary Contacts      | Without             |
| Other Options           | None                |
| Electrical Connection   | Lugs                |
| Height                  | 10.00 in (254 mm)   |
| Depth                   | 5.28 in (134 mm)    |
| Width                   | 5.98 in (152 mm)    |

## Environment

|                        |                                         |
|------------------------|-----------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed<br>CSA                        |

## Ordering and shipping details

|                   |                                |
|-------------------|--------------------------------|
| Category          | 21324 - 8903 S (NOT S*C) MECH. |
| Discount Schedule | CP1                            |
| Gtin              | 785901476917                   |
| Returnability     | No                             |
| Country Of Origin | MX                             |

## Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                        |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 10.00 in (25.4 cm)     |
| Package 1 Width              | 5.98 in (15.2 cm)      |
| Package 1 Length             | 5.28 in (13.4 cm)      |
| Package 1 Weight             | 8.13 lb(US) (3.688 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

|                           |                                                                                                                        |
|---------------------------|------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive         | Not compliant                                                                                                          |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>             |