

# Product data sheet

Specifications



Contactor, Definite Purpose, 20A,  
1 pole, 208/240 VAC 60 Hz 220  
VAC 50 Hz coil, open

8910DP11V09

Discontinued on: Jan 31, 2024

Discontinued

Product availability: Non-Stock - Not normally stocked in  
distribution facility

## Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	20 A
Number Of Poles	1P
Pole Contact Composition	1 NO
Range Of Product	DP

## Complementary

Maximum Horse Power Rating	1 hp 115 V AC, 1 phase 2 hp 230 V AC, 1 phase
Locked Rotor Rated Current	100 A 460 V AC 80 A 575 V AC 120 A 277 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	1 phase
Electrical Connection	Binder head Quick connect terminals

## Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

## Ordering and shipping details

Category	US1CP1B21351
Discount Schedule	CP1B
Gtin	785901073260
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	7.68 oz (217.724 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.