

Product data sheet

Specifications



Contactor, Definite Purpose, 30A, 4 pole, 20HP at 575VAC, 3 phase, 110/120VAC 50/60Hz coil, open

8910DPA34V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 127.50 USD

Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number Of Poles	4P
Pole Contact Composition	4 NO
Range Of Product	DPA

Complementary

Maximum Horse Power Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 15 hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Locked Rotor Rated Current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Binder head Quick connect terminals
Height	3.77 in (95.76 mm) 3.77 in (95.80 mm)
Width	2.75 in (69.85 mm) 2.75 in (69.80 mm)
Depth	3.00 in (76.20 mm) 2.99 in (76 mm)
Net Weight	1.30 lb(US) (0.59 kg) 1.3 lb(US) (0.59 kg)

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	US1CP1B21343
Discount Schedule	CP1B

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	785901073505
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	20.80 oz (589.67 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.