Product data sheet

Specifications





control station type B - 2 operators - Start-Stop (Maintained) - NEMA 7/9

9001BR215

() Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001B
Product Or Component Type	Complete control station
Device Short Name	9001BR
Control Station Application	Start-Stop function
Colour Of Base Of Enclosure	Grey

Complementary

<u> </u>	
Material	Cast zinc
Marking	CE
Type Of Operator	maintained
Control Station Composition	1 push-button, black, white START 1 push-button, red, white STOP
Contacts Type And Composition	2 NO
Mechanical Durability	5000000 cycles
[le] Rated Operational Current	5 A 600 V, AC
Device Mounting	Surface
Type Of Installation	Indoor

Environment

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Nema Degree Of Protection	NEMA 7/9
Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Environmental Characteristic	Hazardous location

Ordering and shipping details Category US10CS121421 Discount Schedule 0CS1 Gtin 785901852186

No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability

Country Of	Origin	
------------	--------	--

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.97 in (35.484 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)
Package 1 Weight	4.00 lb(US) (1.814 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov