Product data sheet

Specifications





Illuminated selector switch head, Harmony 9001K, metal, standard handle, green, 30mm, 2 positions, stay put, 110-120V

9001K11J1G

Product availability: Stock - Normally stocked in distribution facility

Price*: 167.00 USD

Main

Product Or Component Type	Head for illuminated selector switch
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Range Of Product	Harmony 9001K

Complementary

Bezel Material	Metal
Bulb Base	BA 9s
Contacts Type And Composition	Without contact block
Light Block Supply	Via transformer 120 V AC 50/60 Hz
Operator Position Information	2 positions
Operator Profile	Standard handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Maintained
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Type Of Operator	Stay put
Contacts Type And Composition	Without contact block

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785001820840

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	8.64 oz (244.94 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov