Product data sheet

Specifications



() Discontinued

PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001K2L2R21

- () Discontinued on: Dec 2, 2020
- (!) End-of-service on: Dec 31, 2020



Range Of Product	Harmony 9001K	
Product Or Component Type	Complete illuminated push-button	
Device Short Name	9001K	
Mounting Diameter	1.18 in (30 mm)	
Operator Additional Information	Screw-on plastic mushroom	
Light Source	incandescent	

Complementary

Bezel Material	Chromium plated metal	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Red mushroom Ø 57 mm, unmarked	
Bulb Base	BA 9s	
Light Block Supply	Via integral transformer 110120 V AC 25/30 Hz 6 V)	
Mechanical Durability	5000000 cycles	
Operating Position	Any position	
Net Weight	0.37 lb(US) (0.166 kg)	

Environment

Standards	UL 508 EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C 4520 CSA C22.2 No 14 JIS C 852	
Product Certifications	NEMA UL 508	
Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Electrical Shock Protection Class	Class II IEC 61140	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov