





Illuminated selector switch head, Harmony 9001K, metal, without handle, 30mm, 3 positions, stay put, 110 120V

9001K43J1

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 237.00 USD

Main

Product Or Component Type	Head for illuminated selector switch
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Range Of Product	Harmony 9001K

Complementary

Bezel Material	Metal
Bulb Base	BA 9s
Cap/Operator Or Lens Colour	without cap
Contacts Type And Composition	Without contact block
Light Block Supply	Via transformer 120 V AC 50/60 Hz Via transformer 110 V AC 50/60 Hz
Operator Position Information	3 positions
Operator Profile	Without handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Maintained
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Type Of Operator	Stay put
Contacts Type And Composition	Without contact block

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR
	CSA I P24500 class 3211 03

Ordering and shipping details

Category US10CS121426

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CS1
Gtin	785901820857
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.64 oz (244.94 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov