Product data sheet

Specification





Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, white, 30mm, 110-120V

9001KP1W31

Product availability: Stock - Normally stocked in distribution facility

Price*: 153.00 USD

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Pilot light
Device Short Name	K

Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Lens Type	Fresnel plastic
Cap/Operator Or Lens Colour	White
Light Source	incandescent
Bulb Base	BA 9s
Light Block Supply	Via transformer 120 V AC 50/60 Hz Via integral transformer 110 V AC 50/60 Hz
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
Shape Of Screw Head	Round
Operating Position	Any position
Light Source	Incandescent bulb
[Us] Rated Supply Voltage	110120 V AC
Operating Mode	Normal
Device Presentation	Complete product
Lens Type	Fresnel
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Supply Frequency	5060 Hz
Lens Material	Polycarbonate
Size	30 mm

Environment

Product Certifications CSA LR25490 class 3211 03

CE

UL listed file E42259 CCN NKCR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901032076
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	1.80 in (4.572 cm)
Package 1 Weight	7.84 oz (222.26 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov