# Product data sheet

Specifications







# Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, yellow, 30mm, LED yellow, 24-28V

9001KP35LYY31

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 153.00 USD

### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Pilot light	
Device Short Name	К	

### Complementary

Complementary		
Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Lens Type	Fresnel plastic	
Cap/Operator Or Lens Colour	Yellow	
Light Source	Yellow LED	
Bulb Base	BA 9s	
Light Block Supply	Direct 24 V Direct 28 V	
Shape Of Screw Head	Round	
Light Source	LED	
Operating Mode	Normal	
Lens Type	Fresnel	
[Us] Rated Supply Voltage	2428 V	
Light Source Colour	Yellow	
Lens Material	Polycarbonate	
Size	30 mm	

#### Environment

Product Certifications	UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03 CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

# Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901186496	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

# **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.00 oz (226.796 g)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov