

# Product data sheet

Specifications



Head for pilot light, Harmony  
9001K, metal, without cap, 30mm,  
LED red, 120V

9001KP38LR

Product availability: Stock - Normally stocked in distribution facility

Price\*: 143.00 USD

## Main

|                           |                      |
|---------------------------|----------------------|
| Range Of Product          | Harmony 9001K        |
| Product Or Component Type | Head for pilot light |
| Device Short Name         | K                    |

## Complementary

|                             |                 |
|-----------------------------|-----------------|
| Bezel Material              | Metal           |
| Mounting Diameter           | 1.18 in (30 mm) |
| Cap/Operator Or Lens Colour | Without cap     |
| Light Source                | Red LED         |
| Bulb Base                   | BA 9s           |
| Light Block Supply          | Direct 120 V    |
| Shape Of Screw Head         | Round           |
| Light Source                | LED             |
| Operating Mode              | Normal          |
| [Us] Rated Supply Voltage   | 120 V           |
| Light Source Colour         | Red             |
| Size                        | 30 mm           |

## Environment

|                           |   |
|---------------------------|---|
| Product Certifications    | CSA LR25490 class 3211 03<br>CE<br>UL listed file E42259 CCN NKCR |
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13   |

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CS121426 |
| Discount Schedule | 0CS1         |
| Gtin              | 785901033028 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                      |
|------------------------------|----------------------|
| Unit Type Of Package 1       | PCE                  |
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 4.96 oz (140.614 g)  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a> |