





PUSH BUTTON 600VAC 10A 30MM T-K

9001KR1UH4

Discontinued on: May 6, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

Bezel Material	Chromium plated metal
Control Button Type	standard push-button
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Light Source	without
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Full guard in metal

Complementary

Line Rated Current	10 A
Cap/Operator Or Lens Colour	1 black
	1 blue
	1 white
	1 green
	1 red
	1 orange
	1 yellow
Contact Operation	Standard fingersafe
Contacts Type And Composition	4 NO + 4 NC
Control Type	push-button
Electrical Connection	Screw clamp terminal
Light Block Supply	Without supply
.3	Without supply
Marking	unmarked
Mounting Support	panel
Operator Position Information	2 positions
Operator Profile	1 projecting push-button
Permissible Voltage	600 V
Shape	Round head
Type Of Operator	Momentary
Utilisation Category	AC-15
	DC-13

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	00785901847618
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov