

# Product data sheet

Specifications

SQUARE D

Green Premium™



## PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001KR25L

⚠ Discontinued on: Oct 11, 2019

⚠ Discontinued

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Mushroom head push-button
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	Blue mushroom Ø 57 mm, unmarked

### Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.31 lb(US) (0.141 kg)
Operating Position	Any position
Shape Of Signaling Unit Head	Round
Head Material	Plastic
Operator Additional Information	Screw-in with set screw security
Operator Position Information	2 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	5000000 cycles
Device Presentation	Basic element

### Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Standards</b>	EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14
<b>Product Certifications</b>	NEMA UL 508
<b>Vibration Resistance</b>	7 gn 2...500 Hz)IEC 60068-2-6
<b>Shock Resistance</b>	50 gn IEC 60068-2-27

## Ordering and shipping details

<b>Category</b>	21426-9001 K (NOT KA,KM,KX)
<b>Discount Schedule</b>	CS1
<b>Gtin</b>	00785901413356
<b>Returnability</b>	No
<b>Country Of Origin</b>	MX

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

No need of specific recycling operations

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)