Product data sheet

Specifications





30mm Push Button, Type K, push button, no guard, universal

9001KR3U

Product availability: Stock - Normally stocked in distribution facility

Price*: 38.60 USD

Main

| Range Of Product | Harmony 9001K |
|---------------------------------|----------------------|
| Product Or Component Type | Head for push-button |
| Device Short Name | 9001K |
| Operator Profile | projecting, unmarked |
| Operator Additional Information | Without guard |

Complementary

| Mounting Diameter | 1.18 in (30 mm) |
|-------------------------------|-----------------------|
| Shape Of Signaling Unit Head | Round |
| Type Of Operator | spring return |
| Net Weight | 0.20 lb(US) (0.09 kg) |
| Bezel Material | Metal |
| Cap/Operator Or Lens Colour | 7 colours choice |
| Operator Profile | Projecting |
| Type Of Operator | Spring return |
| Contacts Type And Composition | Without contact block |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| Gtin | 785901874911 |
| Returnability | Yes |
| Country Of Origin | MX |

Packing Units

| V | |
|------------------------------|---------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.00 in (5.08 cm) |
| Package 1 Width | 2.30 in (5.842 cm) |
| Package 1 Length | 2.80 in (7.112 cm) |
| Package 1 Weight | 3.68 oz (104.326 g) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Unit Type Of Package 2 | PAL |
|------------------------------|----------------------------|
| Number Of Units In Package 2 | 3200 |
| Package 2 Height | 40.00 in (101.6 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 766.00 lb(US) (347.451 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information


Certifications & Standards

| Reach Regulation | REACh Declaration | | | | |
|---------------------------|--|--|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | | |
| China Rohs Regulation | China RoHS declaration | | | | |
| Environmental Disclosure | Product Environmental Profile | | | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | | | | |
| Circularity Profile | No need of specific recycling operations | | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | | |

Product data sheet

Dimensions Drawings


Dimensions



Mounting and Clearance

Contact Block Mounting Position

Top and Rear views




- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Product data sheet

Panel Cut-Out

Clearance



| Legend plate | a min. | | b min. | |
|--------------|--------|------|--------|------|
| | mm | in. | mm | in. |
| 9001KN2•• | 57.2 | 2.25 | 44.5 | 1.75 |
| 9001KN3•• | 57.2 | 2.25 | 50.8 | 2.00 |

Individual Cut-outs Details

2 alternatives

