





30mm push button, Type K, nonilluminated mushroom button, 1.375 inch yellow, 6A at 120VAC, 1NO/1NC contact, NEMA 4, 13

9001KR4YH13

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 138.00 USD

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	К
Operator Additional Information	Snap-in plastic

### Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Light Source	Without
Light Block Supply	Without supply
Contacts Type And Composition	1 C/O
[le] Rated Operational Current	10 A, AC-15 10 A, DC-13
Contact Operation	Standard
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Yellow
Operator Profile	Mushroom Ø 35 mm
Type Of Operator	Spring return
Size	30 mm

#### **Environment**

Product Certifications	CSA LR 25490 class 3211 03 NEMA UL listed file E42259 CCN NKCR CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	795001022005

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	7.58 oz (215.003 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov