

Product data sheet

Specifications

SQUARE D

Green Premium™



Push-button, Harmony 9001K, metal, snap-in plastic mushroom 35mm, yellow, 30mm, spring return, 1 NO

9001KR4YH5

! Discontinued

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------------------|-----------------|
| Range Of Product | Harmony 9001K |
| Product Or Component Type | Push-button |
| Device Short Name | K |
| Operator Additional Information | Snap-in plastic |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel Material | Metal |
| Mounting Diameter | 1.18 in (30 mm) |
| Light Source | Without |
| Light Block Supply | Without supply |
| Contacts Type And Composition | 1 NO |
| [Ie] Rated Operational Current | 10 A, AC-15 10 A, DC-13 |
| Contact Operation | Standard |
| Device Presentation | Complete product |
| Cap/Operator Or Lens Colour | Yellow |
| Operator Profile | Mushroom Ø 35 mm |
| Type Of Operator | Spring return |
| Size | 30 mm |

Environment

| | |
|---------------------------|----------------------------------------------------------------------------|
| Product Certifications | NEMA CE CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR |
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CS121426 |
| Discount Schedule | 0CS1 |
| Gtin | 785901921073 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|----|
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.08 in (12.903 cm) |
| Package 1 Width | 2.00 in (5.08 cm) |
| Package 1 Length | 12.90 in (32.774 cm) |
| Package 1 Weight | 8.00 oz (226.796 g) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |