



Selector switch head, Harmony 9001K, metal, standard handle, black, 30mm, 2 positions, spring return right to left

9001KS34B

Product availability: Stock - Normally stocked in distribution facility

Price*: 81.00 USD

Main

| Range Of Product | Harmony 9001K | |
|---------------------------|--------------------------|--|
| Product Or Component Type | Head for selector switch | |
| Device Short Name | К | |
| Type Of Operator | spring return | |
| Operator Profile | Black standard knob | |

Complementary

| Bezel Material | Metal | |
|-------------------------------|-----------------------|--|
| Mounting Diameter | 1.18 in (30 mm) | |
| Operator Position Information | 2 positions | |
| Contacts Type And Composition | Without contact block | |
| Device Presentation | Basic element | |
| Cap/Operator Or Lens Colour | Black | |
| Operator Profile | Standard handle | |
| Type Of Operator | Spring return | |
| Size | 30 mm | |
| Return | Right to left | |
| Cam Profile | 4 | |

Environment

| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13 |
|---------------------------|---|
| Product Certifications | CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| Gtin | 785901322597 |
| Returnability | Yes |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.00 in (5.08 cm) |
| Package 1 Width | 2.30 in (5.842 cm) |
| Package 1 Length | 2.80 in (7.112 cm) |
| Package 1 Weight | 4.32 oz (122.47 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |