

Product data sheet

Specifications



Selector switch head, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, stay put

9001KS401B

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Head for selector switch
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Range Of Product	Harmony 9001K

Complementary

Bezel Material	Metal
Cap/Operator Or Lens Colour	black
Contacts Type And Composition	Without contact block
Operator Position Information	3 positions
Operator Profile	Standard handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Maintained
Cap/Operator Or Lens Colour	Black
Type Of Operator	Stay put
Contacts Type And Composition	Without contact block

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901390534
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	2.50 in (6.35 cm)
Package 1 Weight	4.32 oz (122.47 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov